

956 HEAVY DUTY SERIES IGNITION SWITCHES



956-9100



956-3124

Description

Littelfuse Ignition Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

The 956 Heavy Duty Series is our most robust series of Ignition Switches, providing reliable circuit control for vehicle ignition.

Web Resources

Download 2D print and technical resources at:
littelfuse.com/956HeavyDuty

Ordering Information

Features and Benefits

- Key removable in “Off” Position Only (where actuator applicable)
- Ignition Proof to SAE J259

Specifications Overview

Positions:	3-4 Positions
Housing:	Heavy Duty Plated Steel
Ingress Protections:	O-Ring in Shaft and Sealed Terminal Insulator PN: 956-4138: Sealed Terminal Insulator Only

Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles

BULK PART NUMBER	BOXED PART NUMBER	BLISTER PART NUMBER	POSITIONS	MOUNTING	VOLTAGE RATING	INGRESS PROTECTION	ACTUATOR	TERMINATION	SPRING RETURN
956-3124	956-3124-BX	—	Three: Off Ign/Acc - Start	Face Nut through 1.0 (25.4mm) 24 Panel Hole	10A at 12V DC (Acc, Ign/Run), 5A at 12V DC (Start)	O-Ring in Shaft and Sealed Terminal Insulator	Lever (Short)	5 Screws	Spring Return to Ign
956-3126	956-3126-BX	956-3126-BP	Three: Off Acc & Ign - Ign & Start	Face Nut through 1.0 (25.4mm) 24 Panel Hole	10A at 12V DC (Acc & Ign), 5A at 12V DC (Ign & Start)	O-Ring in Shaft and Sealed Terminal Insulator	Hencol Key	4 Screws	Spring Return to Acc & Ign
956-4138	956-4138-BX	—	Four: Acc - Off Ign/Acc - Start	Face Nut through 1.0 (25.4mm) 24 Panel Hole	20A at 12V DC (Acc, Ign/Run), 10A at 12V DC (Start)	Sealed Terminal Insulator	Bitted Key	4 Blades (Aptiv #2962912)	Spring Return to Ign
956-6307	—	—	Three: Acc - Off Ign/Acc	Face Nut through 0.75 (19.05mm) 24 Panel Hole	10A at 12V DC (Acc), 10A at 12V DC (Ign/Run)	O-Ring in Shaft and Sealed Terminal Insulator	Hencol Key	3 Screws	No
956-9100	956-9100-BX	—	Mom Fuel Off - Ign/Acc - Start	Face Nut through 1.0 (25.4mm) 24 Panel Hole	10A at 12V DC (Acc), 5A at 12V DC (Ign/Run, Start)	O-Ring in Shaft and Sealed Terminal Insulator	Hencol Key	5 Screws	Spring Return to Ign/Acc and from Fuel



Visit Littelfuse.com for the most up-to-date product information. Littelfuse products are designed for specific applications and should not be used for any purpose (including, without limitation, automotive applications) not expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse product documentation.