

GLASS 3031

32V IN-LINE SFE AND AGC GLASS FUSE HOLDER



3031-0

Description

The Glass 3031 Series 32V In-Line SFE and AGC Glass Fuse Holder accommodates SFE glass fuses and AGC (3AG) glass fuses up to 20 amps (sold separately).

This holder for glass fuses features an 8" (203mm) looped 14 AWG GPT wire lead that's easy to cut and strip for simple in-line fuse installation.

Large brass contacts help ensure a reliable connection with the installed fuse, while a positive twist-lock seal helps prevent accidental opening.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/3031

Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
3031-0	32V In-Line SFE and AGC Glass Fuse Holder	AGC and SFC FUSE	IN LINE FUSE HOLDER	20 AMPS	32 VDC

Specifications

Current Rating Continuous:	15A
Current Rating Max:	20A
Current Rating Max Terminal:	20A
Fuse Type:	AGC FUSE and SFC FUSE
Flammability Rating:	UL 94 V-2
Mounting Method:	In line Fuse Holder
Max Voltage Rating:	32 VDC
Wire Description:	GPT WIRE COLOR BLACK
Wire Size:	14 AWG

Applications

- Accessory Circuits

Features and Benefits

- Compatible with SFE glass fuses and AGC (3AG) glass fuses up to 20 amps (sold separately)
- 8" (203mm) looped 14 AWG GPT wire lead allows simple in-line fuse holder installation
- Positive twist-lock seal prevents accidental opening
- Large brass contacts maintain a reliable connection with the installed fuse
- Red nylon housing with a UL 94 V-2 flammability rating is suitable for automotive conditions