

FUSES AND THE CONSTRUCTION MARKET



Quality Products, Excellent Service, and Technical Expertise!

Littelfuse offers innovative and quality UL fuses for the commercial construction market. Our UL fuses serve numerous functions to meet your customers most stringent protection needs. Whether indicating or non-indicating, low voltage or high voltage, short circuit to overload protection, Littelfuse has a fuse to fit your application.

Class L: Current limiting protection				
KLPC Series	Time Delay	600 VAC/480 VDC	Up to 6000 Current Amperes AC/DC Rating	
KLLU Series	Time Delay	600 VAC/300 VDC	Up to 4000 Current Amperes AC/DC Rating	
LDC Series (all-purpose AC/DC)	Fast Acting	600 VAC/VDC	Up to 2000 Current Amperes AC/DC Rating	
RK1: Short circuit and overload protection				
LLSRK/LLSRK_ID Series and LLNRK Series	Time Delay	Dual Element	600 VAC/300 VDC and 250 VAC/125 VDC	Up to 600 Current Amperes AC/DC Rating
KLNR/KLSR Series	Fast Acting	250/600 VAC and 125 VDC/250 and 300 VDC	Up to 600 Current Amperes AC/DC Rating	

Our Partner:



RK5: Short circuit and overload protection

FLNR/FLNR_ID Series	Time Delay	Dual Element	250 VAC/125 VDC	Up to 600 Current Amperes AC/DC Rating
FLSR/FLSR_ID Series	Time Delay	Dual Element	600 VAC/300 VDC	Up to 600 Current Amperes AC/DC Rating
IDSR_ID Series	Time Delay	Dual Element	600 VAC/600 VDC	Up to 600 Current Amperes AC/DC Rating

Class J: Maximum protection designed to save space

JTD/JTD_ID Series	Time Delay	600 VAC/500 VDC and 600 VAC/300 VDC	Up to 600 Current Amperes AC/DC Rating
JLS Series	Fast Acting	600 VAC	Up to 600 Current Amperes AC Rating

Class T: Compact size short circuit protection

JLLN Series	Fast Acting	300 VAC/160 and 125 VDC	Up to 1200 Current Amperes AC/DC Rating
JLLS Series	Fast Acting	600 VAC/300 VDC	Up to 1200 Current Amperes AC/DC Rating

Class CC: Small space saving protection of motor circuits

CCMR Series	Time Delay	Dual Element	600 VAC/300 and 500 VDC	Up to 30 Current Amperes AC/DC Rating
KLDR Series	Time Delay	600 VAC/300 VDC	Up to 30 Current Amperes AC/DC Rating	
KLKR Series	Fast Acting	Dual Element	600 VAC/300 VDC	Up to 30 Current Amperes AC/DC Rating

Class CD: Small space saving protection of motor circuits

CCMR Series	Time Delay	Dual Element	600 VAC/250 VDC	Up to 60 Current Amperes AC/DC
--------------------	------------	--------------	-----------------	--------------------------------

Midget: Supplemental overage protection for control circuits

BLF	Fast Acting	250 and 125 VAC	Up to 30 Current Amperes AC
BLN	Fast Acting	250 VAC	Up to 30 Current Amperes AC
BLS	Fast Acting	600 and 250 VAC	Up to 10 Current Amperes AC
FLA	Time Delay	125 VAC	Up to 30 Current Amperes AC
FLM	Time Delay	250 VAC/125 VDC	Up to 30 Current Amperes AC/DC
FLQ	Time Delay	500 VAC/300 VDC	Up to 30 Current Amperes AC/DC
KLK	Fast Acting	600 VAC/500 VDC	Up to 30 Current Amperes AC/DC
KLKD	Fast Acting	600 VAC/VDC	Up to 30 Current Amperes AC/DC
KLQ	Time Delay	600 VAC	Up to 6 Current Amperes AC
FLU	Fast Acting	1000 VAC/VDC	Up to 11 Current Amperes AC/DC



To view Industrial Power and UL Fuses, please scan QR code.

- ★ 5-Star Technical Application Assistance
- ☎ 1-800-TEC-FUSE
- ✉ techline@littelfuse.com

Disclaimer Notice—Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.