

The company named below has been authorized by CSA to represent the products listed in this record as "CSA Certified" and to affix the CSA Mark to these products according to the terms and conditions of the CSA Service Agreement and applicable CSA program requirements (including additional Markings).

File No: 029862 0 000

Class No: 1422 02 FUSES High Rupturing Capacity (HRC) Type

SUBMITTOR

4501292 Littelfuse, Inc.
800 E Northwest Hwy
Des Plaines, IL 60016-3096
USA

FACTORIES

4501292 Littelfuse, Inc.
800 E Northwest Hwy
Des Plaines, IL 60016-3096
USA

4545541 Littelfuse S.A. de C.V.
Calle Nueva Y Poder Judicial
Piedras Negras, Coahuila
Mexico

4545857 Littelfuse, Inc.
100 W Johnson St
Centralia, IL 62801
USA

4545858 Littelfuse, Inc.
215 Egyptian Trail
Arcola, IL 61910
USA

4545859 Littelfuse, Inc.
3 Rutherford Rd
Stephenson Industrial Estate
District 12 Washington
Tyne & Wear, NE37 3HX
United Kingdom

4548889 Littelfuse Phils., Inc.
Lima Technology Center
Special Economic Zone
Lipa City-Malvar
Batangas,
Philippines

December 4, 2002(Replaces:July 9, 2002)

HRC, non-renewable cartridge type:

- Type CCMR, 600V ac and less, 30A and less, Class CC.
- Type FLNR, 541, FLNR-ID, 250V, 600A and less, Class R.
- Type FLSR, FLSR-ID, 560, 600V ac, 300V dc, 600A and less, Class R.
- Type JLLN, 558, 300V, 600A and less, Class T.
- Type JLLS, 559, 600V, 600A and less, Class T, 25.25mm reject feature.
- Type KLDR, 600V, 30A and less, Class CC.
- Type KLKR, 542, 600V, 0.3A - 30A, Class CC.
- Type KLNR, 250V, 600A and less, Class R.
- Type KLSR, 600V, 600A and less, Class R.
- Type LLNRK, 568, 250V, 600A and less, Class R.
- Type LLSRK, 569, 600V, 600A and less, Class R.
- Type IDSR, 600V ac and less, 600V dc and less, 600A and less, Class R.
- Type DCSR, 600V ac and less, 600V dc and less, 30A, Class R.

Class L, non-renewable cartridge type:

- Type KLPC, 566, 600V ac, 601-6,000A.
- Type KLLU, 600V ac, 601-2000A.
- Type LDC, 600V ac and less, 600V dc and less, 800-2000A, IR600V ac-200kA, IR600V dc-50kA.

Class J, time delay non-renewable cartridge type:

- Type JTD, 600V ac and less, 600A and less, IR600-200kA.
- Type JTD-ID, 600V ac and less, 600A and less, IR600-200kA.
- Type JLS, 567, 600V, 600A and less, Class J.

Class G, non-renewable cartridge time-delay fuses:

- Type SLC, rating 0-20A, 600V ac, IR600-100kA, 21-60A, 480V ac, IR480-100kA.

/mg