



JDYX.E67006 Fuses, Supplemental

Fuses, Supplemental

WICKMANN-WERKE GMBH
ANNENSTRASSE 113
58453 WITTEN, GERMANY

E67006

Miniature, cartridge enclosed, nonrenewable.

Type or Cat. No.	Size	Amps	V AC
198 or 19198	5 x 20 mm	0.08-3.5	250
Note: Note: Micro fuse.			
303 or 19303,	7.7 x 6 mm	0.05-5	125
303K or 19303K,			
393 or 19393,	8.5 x 8 x 4 mm	0.05-6.3	125
394 or 19394			
373 or 19373	8.3 x 7.05 mm	0.05-6.3	250
374 or 19374	8.3 x 7.05 mm	0.05-10	250
395 or 19395	8.5 x 8 x 4 mm	0.05-6.3	125
396 or 19396	8.5 x 8 x 4 mm	0.05-6.3	125
419	6.4 x 2.6 mm	0.62-5	125VAC/dc
191 or 19191	5 x 20 mm	0.125-3.5	250
191 or 19191	5 x 20 mm	4-7	125
197 or 19197	5 x 20 mm	0.125-3.5	250
197 or 19197	5 x 20 mm	4-7	125
275 or 19275	1.5 x 5 mm	0.063-7	125 v ac/dc

397 or 19397

8.3 x 3.9 mm

0.350-1.5

125

2002-07-23

This page and all contents are Copyright © 2005 by Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2005 Underwriters Laboratories Inc.®"