






PART NUMBER	COVER OPENING	DIMENSION "A"	FUSE	FUSE QTY/1000	SPLIT WASHER	SPLIT WASHER QTY/1000	HEX NUT	HEX NUT QTY/M	RACHET FASTENER	RACHET FASTENER QTY/1000	STYLE	PART No RENAULT
04980908ZXT	E F	10.54	NO	N/A	NO	N/A	NO	N/A	NO	N/A	2	296712452R---



NOTES:

1. MATERIAL:
- * BODY-GLASS FILLED THERMOPLASTIC: COLOR-BLACK
 - * COVER-THERMOPLASTIC: COLOR-BLACK
 - * HARDWARE-M5 THREADED STUDS & NUTS AND STEEL LOCKWASHER WITH ZINC AND TRIVALENT CHROMATE, LEACHED AND SEALED, INTEGRAL TORQUE CONTROL LUBRICANT FINISH. (MEETS ASTM STANDARD B-117, 96 HR. SALT SPRAY REQUIREMENT).
2. TORQUE REQUIRED FOR MIDI FUSE TERMINAL & CONNECTOR LOCKING NUTS TO BE 4.0-5.0 NEWTON METERS [35-44 IN-LBS]
3. HOLDER MEETS L/F VALIDATION TEST SPEC. VS-005004.
4. PLANT IS ISO 14001 AND ISO TS 16949 CERTIFIED.
5. FUSE IS RoHS COMPLIANT.
6. IMDS AVAILABLE.

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.	
⊙	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
MATERIAL SPEC					
FINISH					
SCALE 1:1					
SUPER DR					
FINISH GOOD WT					
GRAMS/PIECE					
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MK)					
DIMENSION 0.5 - 3 UP TO OVER 3 - 6 UP TO OVER 6 - 30 UP TO OVER 30 - 120 UP TO OVER 120 - 400					
TOLERANCE ±0.1 ±0.1 ±0.2 ±0.3 ±0.5					
3RD ANGLE PROJECTION					
TITLE MIDIFUSE HOLDER					
REVISION DRWG. NO. 04980908ZXTN					
OUTLINE					

LTR	DATE	REVISION	CHK	APD
A	03/07/11	501797ERA-RELEASE OPL		
B	08/31/11	504244ECA-IN NOTES ADD NOTES 4, 5 & 6 OPL		