


MM IN
 .025 .010
 .076 .030
 .101 .040
 .157 .062
 .152 .059
 .203 .080
 .228 .090
 .355 .140
 .482 .190
 .914 .360
 .939 .370
 15.74 .620

46.98 1.850
 46.99 1.850
 3.04 .120
 13.66 .538

COLE-HERSEE CO.
 NPM



RATING AT 12V DC	
ACC	30 AMPS
IGN	10 AMPS
START	10 AMPS

METRIC

- NOTES:
 1. TERMINAL INSULATOR GASKET SEALED.
 2. SHUTTER TYPE SEAL ON LOCK FACE.
 *3. START LOCK-OUT FEATURE; SWITCH MUST GO TO "OFF" POSITION BEFORE START CIRCUIT CAN BE RE-ENERGIZED.
 4. APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259.
 (D) 5 ALL STEEL PARTS PLATED

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV D	SCALE	956-3125 LESS O-RINGS & GND CIRCUIT	DATE DRAWN
				D	NO ADDED/25039	12/20/92	1/11	—	PC	1/29/75		1:1		10-26-76
				C	ECN 25189	8/13/92	1/11	FINISH						
				B	16.01/22457	6-5-84	1/11	—						
				A	HOUSING	8/13/82	1/11							
E	ECN 40137	3/1/00	MA		15 JUL	11/2/16	1/11	TOLERANCES FRACTIONAL ± DECIMAL ±.25					3-POSITION IGN. & START SWITCH	956-3125

SPaulding CO., INC 21-5353