




<u>RATINGS</u>	
MAXIMUM VOLTAGE	8,400 Vac
MAXIMUM CURRENT	84 mA
RESISTANCE	100 kΩ
THERMAL	
8,400 Vac	1 MINUTE ON, 120 MINUTES OFF
1,900 Vac	CONTINUOUS
TORQUE	
TERMINAL N	9.0 N-m (80 in-lb)

NOTES

1. DIMENSIONS IN MILLIMETERS [INCHES]
2. TERMINAL-BLOCK SCREWS: 6-32 x 0.25.
3. MOUNTING SCREWS: M6 OR 0.25-20.
4. USE LIQUID-TIGHT FITTING FOR TERMINAL-BLOCK-ENCLOSURE CABLE ENTRY.
5. CERTIFICATIONS NOT SHOWN.



RELEASE TO WEB	A	15NOV13
DESCRIPTION	REV.	DATE
 Littelfuse		
DWG. NO.	ER-15KV	REV. A