





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.		
ART. NR	DESCRIPTION	NOTE
178.6115.000_	FH2 HOLDER HUSING	-

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300036. INITIAL RELEASE. DSILVA	3/7/2022	L.ARGIL.




NOTES:
1. MATERIAL: THERMOPLASTIC, COLOR BLACK

NO.	COMPONENT NO.	COMPONENT NAME		QTY U							
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)											
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400							ANGLE
±0.05	±0.05	±0.1	±0.15	±0.2							NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS.
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

PER CHI-NP20-0008 PROCEDURE		FIT/ FUNCTION CRITICAL CHARACTERISTICS
	<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
	CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
		DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
	CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

		NAME	DATE	Littelfuse® Expertise Applied Answers Delivered	
DRAWN	D.SILVA	1/14/2022			
CHECKED	-		-		
	-		-		
	-		-	TITLE	
FORM NO: CVP-PE40-0003 REV B					
THIRD ANGLE PROJECTION				FH2 HOLDER HOUSING	
		SIZE B	DWG. NO. OUTLINE	OL-178.6115.0000	REV. A
DO NOT SCALE DRAWING			SCALE 2:1		SHEET 1 OF 1