

MM	IN
.51	.020
1.52	.060
2.79	.110
3.43	.135
4.83	.19
5.59	.22
9.40	.37
16.76	.66
35.05	1.38
43.94	1.73
52.58	2.07

TBE# 1006


EX 13715

GASKET NEOPRENE
OR EQUIVALENT

VIEW OF SECTION A
SCALE 2=1

SPRING RETURN TO OFF OFF SPRING RETURN TO OFF

B & GL 40° 40° B-GL & ST



80101-A LEVER

8302 HEX NUT


BUSHING - 5/8 - 32 - 2ATHD

LOCATING PIN

CASE

TERMINAL - 3 REQ'D

WASHER HD. SCREW #10-32THD
W/ SHAKEPROOF L WASHER
3 REQ'D



HENCOL SEAL #11
SHOWN CROSS HATCHED

METRIC

LEGEND

ST	START
GL	GLOW
B	BATTERY

6. ARC DEFLECTING LIFT
OFF FEATURE

NOTES: 1. ALL STEEL PARTS PLATED @

2. 1/8" RING SEALED AT MTG. BUSHING
3. ● DENOTES SILVER CONTACT SURFACES
4. IDENTIFICATION LETTERS HOT STAMPED
5. SILVER CADMIUM OXIDE CONTACT POINTS
DO NOT SCALE

LET.	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV'D	SCALE	DATE DRAWN
								N/A	EA		N/A	FULL	3-19-65
								FINISH					DATE BLUEPRINT
								N/A					
				P	FCN 99593	4/21/64	JF						
				N	CAD OR ZINC / 25239	11/29/62	JH	TOLERANCES					
				M	REDRAWN	8/10/89	RO	DECIMAL ± N/A METRIC ± N/A					
SWITCH, HEAT & START													95033

CH-188(4-78)