

ATO® AFH SERIES

32V IN-LINE WIRE-LEADED PANEL-MOUNT FUSE HOLDER



Description

The ATO® AFH Series 32V In-Line Wire-Leaded Panel-Mount Fuse Holder can be used for either in-line installation or panel-mounting applications thanks to the 8" looped lead wire and the snap fit gripping arms.

Designed with a 14 AWG black lead wire, the ATO® AFH Series fuse holder is compatible with ATO® blade-style fuses (sold separately) up to 20 amps. The interlocking, heat-stabilized nylon fuse holder body allows you to snap multiple fuse holders together.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/AFHFuseHolders

Applications

- Heavy-Duty Automotive Fusing

Features and Benefits

- Accepts ATO® blade-style fuses (sold separately) up to 20 amps
- Interlocking fuse holder body lets you connect multiple fuse holders
- Heat-stabilized black nylon body has a UL 94 V-2 flammability rating
- 8" looped 14 AWG black lead wire allow simple in-line installation
- Gripping arms enable optional panel mounting

Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
0AFH0001XP W/O FUSE	32V In-Line Wire-Leaded Panel-Mount Fuse Holder - 20A, 14 AWG - Blister Pack - 100 Pcs.	ATO	IN LINE FUSE HOLDER	20 Amps	32 VDC
0AFH0001Z W/O FUSE	32V In-Line Wire-Leaded Panel-Mount Fuse Holder - 20A, 14 AWG	ATO	IN LINE FUSE HOLDER	20 Amps	32 VDC

Specifications

Continuous Current Rating:	15A
Max Current Rating:	20A
Max Current Rating Terminal:	20A
Fuse Type:	ATO®
Ignition Protection:	V-2
Ignition-Proof:	UL 94
Input Terminals:	ATO FUSE BLADES
Mounting Method:	IN LINE FUSE HOLDER
Output Terminals:	WIRE WITH TERMINALS INCLUDED
Max Voltage Rating:	32 VDC
Wire Description:	VINYL PLASTIC INSULATED ANNEALED COPPER CABLE
Wire Size:	14 AWG

PN: 0AFH0001XP

The ATO® AFH Series 32V In-Line Wire-Leaded Panel-Mount Fuse Holder can be used for either in-line installation or panel-mounting applications thanks to the 8" looped lead wire and the snap fit gripping arms. This configuration (0AFH0001XP) is rated for up to 20-amp ATO® blade fuses (sold separately) and features a black 14 AWG looped lead wire. Carded blister packaging allows simple retail display.

Features and Benefits

- Accepts ATO® blade-style fuses (sold separately) up to 20 amps
- Black 14 AWG looped lead wire
- Carded blister packaging for easy retail display

PN: 0AFH0001Z

The ATO® AFH Series 32V In-Line Wire-Leaded Panel-Mount Fuse Holder can be used for either in-line installation or panel-mounting applications thanks to the 8" looped lead wire and the snap fit gripping arms. This configuration (0AFH0001Z) is rated for up to 20-amp ATO® blade fuses (sold separately) and features a black 14 AWG looped lead wire.

Features and Benefits

- Accepts ATO® blade-style fuses (sold separately) up to 20 amps
- Black 14 AWG looped lead wire