

Special Products

ATO™ Resistor

Part Number: 240100 Series



Specifications

Operating Temp.: -20°C to +85°C

Resistor Value: Optional

Power Rating: 1/4 W Max

Body Material: Thermoplastic

Term. Material: C.R.S. (Ni/Zn Plated)

Term. Retention: 25 N

ATO™ Diode

Part Number: 240103



Specifications

Operating Temp.: -40°C to +85°C

Diode Rating: 1.0 A

Max P.I.V.: Optional

Body Material: Thermoplastic

Term. Material: C.R.S. (Ni/Zn Plated)

Term. Retention: 25 N

MINI™ Resistor

Part Number: 240100 Series



Specifications

Operating Temp.: -40°C to +85°C

Resistor Value: Optional

Power Rating: 1/4 Max

Body Material: Thermoplastic

Term. Material: C.R.S. (Ni/Zn Plated)

Term. Retention: 25 N

MINI™ Diode

Part Number: 240113



Specifications

Operating Temp.: -40°C to +85°C

Diode Rating: 1.0 A

Max P.I.V.: Optional

Body Material: Thermoplastic

Term. Material: C.R.S. (Ni/Zn Plated)

Term. Retention: 25 N

ATO™ Shunt

Part Number: 240094



Specifications

Operating Temp.: -40°C to +125°C

Maximum Continuous Load Rating: 35 A

Body Material: Thermoplastic (UL 94V0 Rated)

Term. Material: Brass Tin Plated

MINI™ Shunt

Part Number: 297900



Specifications

Operating Temp.: -40°C to +125°C

Maximum Continuous Load Rating: 20 A

Body Material: Thermoplastic (UL 94V0 Rated)

Term. Material: Zinc Silver Plated

JCASE™ Shunt

Part Number: 495900



Specifications

Operating Temp.: -40°C to +125°C

Maximum Continuous Load Rating: 50 A

Body Material: Nylon

Term. Material: Copper