# **PAL Fuses**



# AUTO LINK PAL FUSES - 293





#### **Description**

PAL fuses are commonly found on many Japanese and domestic built vehicles.

## **Specifications**

Voltage Rating:	32 VDC	
Current Cycling:	24°C	
The fuses satisfy the performance requirements after 50% of the rated current		
is applied for 10,000 cycles. Each cycle consists of an interrupted current with		
the pattern of 5 minutes ON and 10 minutes OFF.		
Operating Temperature Range:	-40°C to +125°C	

Complies with JASO 0612

# **Ordering Information**

Part Number	Package Size	
0293xxx.H	100	
0293xxx.U	500	
0293xxx.MXJ	1000	

# **Time-Current Characteristics**

% of Rating	Opening Time Min / Max (s)
110	14,400 s
200	5 s / 100 s
350	0.2s / 7 s
600	0.040 s / 1 s

#### Ratings

Part Number	Current Rating (A)	Body Color
0293020	20	LIGHT BLUE
0293030	30	PINK
0293040	40	GREEN
0293050	50	RED
0293060	60	YELLOW
0293070	70	BROWN
0293080	80	BLACK
0293100	100	BLUE

### **Dimensions**

Dimensions in mm





