


AUTO LINK PAL FUSES - 295





Description

PAL fuses are commonly found on many Japanese and domestic built vehicles.

Specifications

Voltage Rating: 32 VDC Current Cycling: 24°C

The fuses satisfy the performance requirements after 50% of the rated current is applied for 10,000 cycles. Each cycle consists of an interrupted current with the pattern of 5 minutes ON and 10 minutes OFF.

Operating Temperature Range: -40°C to +125°C

Complies with JASO 0612

Ordering Information

Part Number	Package Size	
0295xxx.H	100	
0295xxx.U	500	
0295xxx.MXJ	1000	

Time-Current Characteristics

% of Rating	Opening Time Min / Max (s)	
110	14,400 s	
200	5 s / 100 s	
350	0.2s / 7 s	
600	0.040 s / 1 s	

Ratings

Part Number	Current Rating (A)	Body Color
0295020	20	LIGHT BLUE
0295030	30	PINK
0295040	40	GREEN
0295050	50	RED
0295060	60	YELLOW
0295070	70	BROWN
0295080	80	BLACK
0295100	100	BLUE
0295120	120	WHITE
0295140	140	REDDISH BROWN

Dimensions

Dimensions in mm

