

Out of thermoplastic (UL 94-V0, heat-resistant)

(4 pins each), copper alloy, tinned

Black

**Ordering Information** 

Part Number

**Dimensions** 

178.4265.0002

Leaf spring connector systems, soldering terminals

**Package Size** 

500

RoHS


## FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 58V



#### **Description**

PCB Fuse Holder for 42V PowerNet with coding for TAC fuseslinks. For through hole soldering. Rated voltage 58V.

#### **Recommended Assembly**



Note: The locking feature at the holder center must lock holder and PCB before welding.

#### Ratings

Part Number	Description	Contact Temperature
178.4265.0002	Complete	max. 130°C



Visit **Littelfuse.com** for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.

# 


1.2


**Specifications** 


Housing:


Color:

Connections:











RoHS


# FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 80V




#### **Description**

PCB Fuse Holder for ATO / FKS size fuse-links. For through hole soldering. Rated voltage 80V.

#### **Recommended Assembly**





Note: The locking feature at the holder center must lock holder and PCB before welding.

#### Ratings

Part Number	Description	Contact Temperature
178.6165.000_	Complete	max. 130°C



Visit **Littelfuse.com** for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.

#### **Specifications**


Housing:	Out of thermoplastic (UL 94-VO, heat-resistant)
Connections:	Leaf spring connector systems, soldering terminals
	(4 pins each), copper alloy, silver plated
Color:	Black


#### **Ordering Information**


Part Number	Package Size
178.6165.xxx1	100
178.6165.xxx2	500


#### **Dimensions**

Dimensions in mm












# FLR PCB FUSE HOLDER FOR ATO® STYLE BLADE FUSE RATED 80V





#### **Specifications**

Housing:	Out of thermoplastic (UL 94-VO, heat-resistant)
Connections:	Leaf spring connector systems, soldering terminals
	copper alloy, tin plated
Color:	Black


#### **Ordering Information**

Part Number	Package Size
178.6164.xxx1	100
178.6164.xxx2	500

#### **Description**

PCB Fuse Holder for ATO/FKS size fuse-links. For through hole soldering. Rated voltage 80V

#### **Recommended Assembly**




Note: The locking feature at the holder center must lock holder and PCB before welding.


#### Со Со

s,

Part Number	Package Size
178.6164.xxx1	100
178.6164.xxx2	500

### **Dimensions in mm**







**Part Number** Description **Contact Temperature** 178.6164.000\_ Complete max. 130°C



**Ratings** 

Visit Littelfuse.com for the most up-to-date product information. Littelfuse reserves the right to make product changes, without notice. Material in this document is as accurate as known at the time of publication.