

IN-LINE GLASS FUSEHOLDERS

150322





Description

The 150322 is a 500 VAC/125 VDC rated inline fuseholder ideal for applications where supplemental protection is needed, such as lighting ballasts and power supplies. 8-inch pre-stripped wire leads and fuse clips come preassembled for quick installation.

Features/Benefits

- Single piece body minimizes component count
- High voltage rating accommodates many power applications
- Wire leads are pre-attached to fuse clips for quick assembly
- Single piece molded body
- UL Recognized

Recommended Fuses

3AG (312, 313 Series) 3AB (314, 326, 505 Series)

Dimensions in mm (inches)



| Voltage Rating: | 500 VAC, 125 VDC | |
|------------------------|---------------------------------|--|
| Ampere Rating: | 15 A | |
| Fuse Type: | 1⁄4″ x 11⁄4″ | |
| Fuse Clips: | Tin-plated brass | |
| Wire: | Black 18 AWG, 150° C Stranded | |
| Molded Body: | Single piece thermoplastic | |
| Flammability Rating: | UL94 V-0 | |
| Approvals: | UL Recognized (File No. E14721) | |
| Environmental: | RoHS complaint and Pb free | |
| Storage Temperature: | -40° C to 80° C | |
| Operating Temperature: | -55° C to 125° C | |

Ordering Information

| CATALOG NUMBER | SYSTEM NUMBER | STANDARD PACK |
|----------------|---------------|---------------|
| 150322 | 01500322H | 100 PIECES |

Web Resources

Sample requests, downloadable CAD drawings and other technical information: **www.littelfuse.com/150322**

Additional In-Line Glass Fuseholders

Twist-Lock 155 Series RoHS

In-Line Mount

Low Voltage 3AG, SFE

Heavy-Duty Bayonet 155 Series RoHS PO In-Line Mount

Low Voltage 3AG


Special Type 150 Series RoHS (Mount In-Line Mount

2AG, 5x20mm





Dimensions in (inches)





Web Resources

For more information, visit: www.littelfuse.com/150 www.littelfuse.com/155

