

# Military Midget 10x38 mm Fuses

## 592S Series

Commercial Equivalent = [KLK Series](#)



### Description

With a vast network of manufacturing and engineering facilities and a global system of distribution channels, Littelfuse offers a variety of switchgear fuses to meet your specific needs, including military high-reliability fuses.

### Features & Benefits

FEATURES	BENEFITS
<b>10x38 mm size</b>	Common dimensions used in a variety of applications
<b>Fast-acting</b>	Provides fast, reliable short-circuit response within the interrupting rating
<b>POWR-GARD® technology</b>	Ensures quality overcurrent protection

### Applications

- Control circuits
- Street and HID lighting
- Computers

### Approved to MIL-PRF-15160/60

MIL TYPE DESIGNATION	SILVER-PLATED CAPS	MIL TYPE DESIGNATION	SILVER-PLATED CAPS
60C 500V ¼AS	<b>592.125S</b>	F60C 500V 3AS	<b>592 003S</b>
F60C 500V ⅜AS	<b>592.200S</b>	F60C 500V 4AS	<b>592 004S</b>
F60C 500V ½AS	<b>592.250S</b>	F60C 500V 5AS	<b>592 005S</b>
F60C 500V ¾AS	<b>592.300S</b>	F60C 500V 6AS	<b>592 006S</b>
F60C 500V 1AS	<b>592.375S</b>	F60C 500V 8AS	<b>592 008S</b>
F60C 500V 1½AS	<b>592.500S</b>	F60C 500V 10AS	<b>592 010S</b>
F60C 500V 2AS	<b>592.750S</b>	F60C 500V 15AS	<b>592 015S</b>
F60C 500V 3AS	<b>592 001S</b>	F60C 500V 20AS	<b>592 020S</b>
F60C 500V 4AS	<b>592 01.5S</b>	F60C 500V 25AS	<b>592 025S</b>
F60C 500V 5AS	<b>592 002S</b>	F60C 500V 30AS	<b>592 030S</b>

Note: Boldface numbers indicate series; light type numbers indicate amperage value.

**Disclaimer Notice** – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/product-disclaimer](http://www.littelfuse.com/product-disclaimer).