


**T 3,15 A L 250V**

**Speed:**  
T = Time Delay  
F = Fast  
M = Medium  
TT = Very slow  
FF = Very fast

**Current Rating:**  
1A, 5A, 32mA (.032A)

**Breaking Capacity:**  
L = Low (glass)  
H = High (ceramic)  
E = Enhanced (glass)

**Voltage Rating:**  
Maximum circuit voltage at  
rated interrupting current