




MATERIALS

BODY: NYLON, BLACK

TERMINALS: BRASS

WIRE: #16 AWG. GPT WIRE PER SAE J1128.

NOM. O. D. . 104, COLOR: RED.

MAX. RATINGS:

2AG FUSES: 5 AMP., 350V.

5x20 FUSES: 10 AMP., 350V.

RAI CERTIFY

THIS PRINT COVER THE FOLLOWING PART NUMBER:

01500274Z

01500274LXN

●	DENOTES CRITICAL CHARACTERISTICS.	UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE	
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.	
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.	

COPIES TO		MATL SPEC		FINISH	
1	9	18	DRW	JMB	DATE 1/23/98
2	10	19	CHK		SCALE 4=1
3	12	20	APPD		SUPER DRW
4	13	21		DATE	RAW STK WT
5	14	23			LBS/M
6	15	33	TOLERANCE UNLESS OTHERWISE SPECIFIED		
7	16	43	TWO PLACE DEC ±.01		
8	17	53	THREE PLACE DEC ±.005		
			TITLE		
			2AG/5 x 20 IN-LINE FUSEHOLDER		
			REVISION		OUTLINE
			DRAWG NO.		01500274Z
					
			DES PLAINES, ILLINOIS 60016		