


- NOTES:
1. MAX. RATING 30A, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
 3. WIRE: 12 GA, COLOR: ORANGE

CUSTOMER: FORD
CUSTOMER P/N: 1W1T-14517-AA

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		FINISH		
1	9	DRW	DATE 01/24/00	SCALE 1:1
2	10	19	CR	SUPER DRW
3	12	20	CHK	DATE
4	13	21	APPD	DATE
5	14	23		RAW STK WT
6	15	33		LBS/M
7	16	43	TOLERANCE UNLESS OTHERWISE SPECIFIED	
8	17	53	THREE PLACE DEC ±.01 FRACTION ±	
			ANGULAR ±1°	
TITLE				
MINIFUSE HOLDER, IN LINE				
LTR		REVISION		CHK APD
A	60197-RELEASE 01/24/00 PJM			
B	80686D-CHG 26.7 TO 27.1 & 21.6 TO 23.6 07/07/00 PJM			


Littelfuse
 DES PLAINES, ILLINOIS 60016
 DRAWING NO. 01530024Z
 OUTLINE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE ----
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. THE PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC IS LOCATED IN THE INSTRUCTIONS.
 DENOTES CP DIMENSIONS--MINIMUM CP VALUE
 DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS ABOVE ARE FOR DIMENSIONS MEASURED WITHIN THE DIMENSIONAL LIMITATIONS FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT