

Technical drawing of a .01MF capacitor assembly, showing dimensions and material specifications.

Top View Dimensions:

- Overall width: 13.25
- Overall height: 14.75
- Terminal spacing: 10.9
- Terminal width: 3.8
- Terminal height: 4.14
- Terminal base height: 4.90

Material and Marking:

- BLACK HOT FOIL STAMP .01MF WITH NEW GOTHIC CHARACTERS 1.98 HIGH THIS SURFACE
- DATE CODE PER JULIAN CALENDAR 4 DIGIT SYSTEM LOCATION OPTIONAL EITHER SIDE
- BODY: THERMOPLASTIC COLOR: YELLOW
- TERMINALS: STEEL NICKEL/ZINC PLATED

Side View Dimensions:

- Overall height: 13.2 - 13.8
- Terminal height: 7.5
- Terminal width: 3.4 - 4.0
- Terminal angle: 90° ± 1°
- Terminal base width: 0.4
- Terminal base height: 0.86
- Terminal base thickness: 0.79

End View Dimensions:

- Overall width: 10.9 ± 0.3
- Terminal width: 2.8 ± 0.15
- Terminal angle: 15°
- Terminal base width: 0.7 TYP.
- Terminal base height: 0.7

Notes:

- CERAMIC CAPACITOR: .01MF ±10% 100V.
- ASSEMBLY TO MEET REQUIREMENTS OF LITTELFUSE SPEC. VS012001.

METRIC

[illegible]