


PART NUMBER	LENGTH "L"	DIAMETER "A"
03540518Z	3.0 inches [76.2 mm]	0.22 inches [5.59 mm]
03540541Z	2.5 inches [63.5 mm]	0.22 inches [5.59 mm]



NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

©	DENOTES CRITICAL CHARACTERISTICS.
---	-----------------------------------

CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
-----	--

ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
----	---

CP

DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

METRIC
COMPONENT

										MATL SPEC										NYLON 6/6, 13% GF, BLACK									
COPIES TO										FINISH																			
1	9	18											DRW	RLDJ	DATE	03/18/11	SCALE	1:1											
2	10	19											CHK		DATE		SUPER DR												
3	12	20											APPD		DATE		FINSH GOOD WT												
4	13	21											GRAMS/PIECE																
5	14	23											TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fh)																
6	15	33											DIMENSION																
7	16	43											TOLERANCE																
8	17	53											3RD ANGLE PROJECTION																
										TITLE										MOUNTING LEG									
										NARROW PROFILE, 1.38 WIDE																			
										REVISION										DRWG. NO.									
																				A									
										LIPA CITY, BATANGAS, PHILIPPINES										OL-03540500Z									