


Architectural floor plan of a rectangular room. The overall dimensions are 76.20 (width) by 38.10 (depth). The room features a central area with a grid of cross-shaped symbols, likely representing columns or structural elements. The plan includes various dimension lines and labels:

- Overall width: 76.20
- Overall depth: 38.10
- Top horizontal offset: 3.00
- Left vertical offset: 19.05
- Right vertical offset: 1.50
- Bottom horizontal offset: 2.24
- Internal width dimension: 56.90
- Internal depth dimension: 19.05
- Small square symbols are located at the corners and along the perimeter of the room.



CERTIFICATION OF  
COUNTRY OF ORIGIN  
REQUIRED

|                                                         |    |                                                   |  |
|---------------------------------------------------------|----|---------------------------------------------------|--|
| COPIES TO                                               |    | MAT'L SPEC.                                       |  |
| 1                                                       | 18 | Nylon: Cncr. Dcr.                                 |  |
| 2                                                       | 10 | FINISH                                            |  |
| 3                                                       | 19 | SCALE                                             |  |
| 4                                                       | 20 | DR.                                               |  |
| 5                                                       | 21 | CHK.                                              |  |
| 6                                                       | 23 | APPD.                                             |  |
| 7                                                       | 33 | DATE                                              |  |
| 8                                                       | 43 | RAW STK. WT.                                      |  |
| 9                                                       | 53 | LBS./M                                            |  |
| TITLE                                                   |    | TOLERANCE UNLESS OTHERWISE SPECIFIED              |  |
| 2 POSITION ISO RELAY MODULE                             |    | TWO PLACE DEC. $\pm .50mm [0.007]$ FRACTION $\pm$ |  |
|                                                         |    | THREE PLACE DEC. $\pm .25mm [0.01]$ ANGULAR $\pm$ |  |
| LITTELFUSE                                              |    | DRWC                                              |  |
| 800 E. NORTHWEST HIGHWAY<br>DES PLAINES, ILLINOIS 60016 |    | D 03540536Z                                       |  |