


NOTES:

- INTERRUPT RATING: 2000A @ 32VDC
VOLTAGE RATING: 32VDC
TEMP. RATING: -40°C - 125°C
CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NO		COMPONENT NO	DESCRIPTION		QTY/M	U/M					
BILL OF MATERIAL											
MATERIAL SPEC			FINISH								
COPIES TO			DATE	SCALE	FULL						
1	9	18	DATE	DATE	SUPER DRW						
2	10	19	CHK	DATE	FINISH GOOD WT						
3	12	20	APPD	DATE	GRAMS/PIECE						
4	13	21	TOLERANCE UNLESS OTHERWISE SPECIFIED								
5	14	23									
6	15	33	TWO PLACE DEC ±.25[.01] FRACTION ±								
7	16	43									
8	17	53	THREE PLACE DEC ±.100[.004] ANGULAR ±1°								
3RD ANGLE PROJECTION											
TITLE			CABLEPRO								
REVISION			DRWG NO.	OUTLINE							
C			0496200.7XK								
LITTELFUSE			DES PLAINES, ILLINOIS 60016								

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

NOTES:

1. DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE

2. DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND PACKAGING MUST BE DEFINED IN INSTRUCTIONS.

3. DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

4. DIMENSIONS MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SPECIFIED IN THE DRAWING AND INITIALLY LOCATED TO THE DRAWING FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT