



% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

- INTERRUPT RATING: 2000A @ 32VDC
- VOLTAGE RATING: 32VDC
- TEMP. RATING: -40°C - 125°C
- CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
- SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
- APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
- BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS ON ONE OF THE CABLE LEADS.

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATERIAL SPEC			
1	9	18	DRW	DATE	05/07/07
2	10	19	DWM	SCALE	FULL
3	12	20	CHK	DATE	SUPER DRW
4	13	21	APPD	DATE	FINISH GOOD WT
5	14	23	APPD	DATE	GRAMS/PIECE
6	15	33			
7	16	43			
8	17	53			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
TWO PLACE DEC ±.25[.01] FRACTION ±					
THREE PLACE DEC ±.100[.004] ANGULAR ±1°					
3RD ANGLE PROJECTION		TITLE			
		CABLEPRO			
		DRWG. NO. 0496200.ZXAN			
		OUTLINE			

LTR	REVISION	CHK	APD
A	63230 - RELEASED 05/07/07 DHM		
B	85493D- CHG. RELEASE DATE FROM 05/07/06. 05/22/07 DHM		

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT OF CPK VALUE IS GIVEN IN THE INSTRUCTIONS.
 DIMENSIONS CP DIMENSIONS, -MINIMUM CP VALUE
 DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SHOWN IN THIS DRAWING AND INITIALLY LOCATED TO THE RIGHT OF THE DIMENSION LINE ARE FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT

