



% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

- INTERRUPT RATING: 2000A @ 32VDC
- VOLTAGE RATING: 32VDC
- TEMP. RATING: -40°C - 125°C
- CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
- SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
- APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
- BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS ON ONE OF THE CABLE LEADS.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND PACKAGING TO BE DEFINED IN INSTRUCTIONS.
 DENOTES CP DIMENSIONS.-MINIMUM CP VALUE
 DIMENSIONS TO BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO THE DRAWING FOR MAXIMUM TOOL LIFE.

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATERIAL SPEC			
1	9	DRW	DATE	06/07/07	SCALE
2	10	19	DHM		FULL
3	12	20	CHK		SUPER DRW
4	13	21	APPD		FINISH GOOD WT
5	14	23			GRAMS/PIECE
6	15	33			
7	16	43			TOLERANCE UNLESS OTHERWISE SPECIFIED
8	17	53			TWO PLACE DEC ±.25[.01] FRACTION ±
					THREE PLACE DEC ±.100[.004] ANGULAR ±1°
					TITLE
					CABLEPRO
					DRWG. NO.
					0496200.ZXAP
					OUTLINE
					REVISION
					A
					LITTELFUSE®
					DES PLAINES, ILLINOIS 60016

LTR	REVISION	CHK	APD
A	63277 - RELEASED 06/07/07 DHM		

UNCONTROLLED DOCUMENT