



% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

INTERRUPT RATING: 2000A @ 32VDC
 VOLTAGE RATING: 32VDC
 TEMP. RATING: -40°C - 125°C
 CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
 SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
 APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
 BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS ON ONE OF THE CABLE LEADS.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT OF CPK VALUE IS GIVEN IN THE LITTELFUSE PRODUCT INSTRUCTIONS.
 CP DIMENSIONS, -MINIMUM CP VALUE
 DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS OF THIS DRAWING AND INITIALLY LOCATED TO THE RIGHT OF THE DIMENSION LINE ARE FOR MAXIMUM TOOL LIFE.

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATERIAL SPEC			
1	9	18	DRW	DATE	04/22/08
2	10	19	DHM	SCALE	FULL
3	12	20	CHK	DATE	SUPER DRW
4	13	21	APPD	DATE	FINISH GOOD WT
5	14	23		DATE	GRAMS/PIECE
6	15	33			
7	16	43			TOLERANCE UNLESS OTHERWISE SPECIFIED
8	17	53			TWO PLACE DEC ±.25 [.01] FRACTION ±
					THREE PLACE DEC ±.100 [.004] ANGULAR ±1°
TRIPLE ANGLE PROJECTION		TITLE			
		CABLEPRO			
LTR		REVISION			CHK
A	000366ER	04/22/08	RELEASED	DHM	

REVISION A

DRWG. NO. 0496200.ZX8

OUTLINE

Littelfuse
DES PLAINES, ILLINOIS 60016

UNCONTROLLED DOCUMENT