


% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

INTERRUPT RATING: 2000A @ 32VDC
 VOLTAGE RATING: 32VDC
 TEMP. RATING: -40°C TO +150°C
 CABLE TYPE: IRRADIATED XLPE, 4 AWG, PER MS-9502 / YPES-25-08-245
 SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
 APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
 BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS ON ONE OF THE CABLE LEADS.



NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATERIAL SPEC			
1	9	18	DRW	DATE	02/24/06
2	10	19	CHK	DATE	SCALE FULL
3	12	20	CHK	DATE	SUPER DRW
4	13	21	APPD	DATE	FINISH GOOD WT GRAMS/PIECE
5	14	23	APPD	DATE	TOLERANCE UNLESS OTHERWISE SPECIFIED
6	15	33			TWO PLACE DEC ±.25 [.01] FRACTION ±
7	16	43			THREE PLACE DEC ±.100 [.004] ANGULAR ±1°
8	17	53			
TRD ANGLE PROJECTION		TITLE			
CABLEPRO		CABLEPRO			
REVISION		DRAWG. NO.		OUTLINE	
A		0496200.ZXAC			

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC IS GIVEN IN THE INSTRUCTIONS.
 DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS AND LOCATIONS WITHIN THE DIMENSIONAL LIMITATIONS ARE FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT

