



RIVETS (4X)
 WHITE HOT STAMP ONE SIDE (SEE CHART)
 BAR CODE OR DATE CODE (SEE NOTES)

% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:
 INTERRUPT RATING: 2000A @ 32VDC
 VOLTAGE RATING: 32VDC
 TEMP. RATING: -40°C - 125°C
 CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
 SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
 APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
 BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
MATERIAL SPEC		FINISH			
COPIES TO	DRW	PJM	DATE	SCALE	FULL
1	9	18	12/03/03	12/03/03	FULL
2	10	19		SUPER DRW	
3	12	20		FINISH GOOD WT	GRAMS/PIECE
4	13	21		TOLERANCE UNLESS OTHERWISE SPECIFIED	
5	14	23		TWO PLACE DEC ±.25 [0.01]	FRACTION ±
6	15	33		THREE PLACE DEC ±.100 [0.004]	ANGULAR ±1°
7	16	43			
8	17	53			
3RD ANGLE PROJECTION		TITLE			
		CABLEPRO			

LTR	REVISION	CHK	APD
A	61316 - RELEASED 12/03/03 PJM		
B	83705B- ADDED BAR CODE 5/21/04	JMB	
C	83927B - CHG. DIM'S 9/21/04 BJJ		
D	84765B-ADD NOTES FOR BAR CODE 05/31/06	DHM	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES.
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND PACKAGING TO BE DEFINED IN INSTRUCTIONS.
 DIMENSIONS TO BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO FOR MAXIMUM TOOL LIFE.

REVISION D
 DRAWG. NO. 0496200.7XM
 OUTLINE
 LitteLfuse®
 DES PLAINES, ILLINOIS 60016

UNCONTROLLED DOCUMENT