



% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

- INTERRUPT RATING: 2000A @ 32VDC
- VOLTAGE RATING: 32VDC
- TEMP. RATING: -40°C TO +150°C
- CABLE TYPE: IRRADIATED XLPE, 4 AWG, PER MS-9502 / YPES-25-08-245
- SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
- APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
- BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS ON ONE OF THE CABLE LEADS.

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M	
BILL OF MATERIAL						
COPIES TO		MATERIAL SPEC				
1	9	18	DRW	SCALE	02/24/06 FULL	
2	10	19	CHK	DATE	SUPER DRW	
3	12	20	APPD	DATE	FINISH GOOD WT	
4	13	21		DATE	GRAMS/PIECE	
5	14	22		DATE		
6	15	23		DATE		
7	16	24		DATE		
8	17	25		DATE		
TOLERANCE UNLESS OTHERWISE SPECIFIED						
TWO PLACE DEC ±.25[.01] FRACTION ±						
THREE PLACE DEC ±.100[.004] ANGULAR ±1°						
TITLE						
CABLEPRO						
LTR		REVISION			CHK	APD
A		61921 - RELEASED 03/06/06 DJG				
DRAWG. NO.		0496200.ZXAD				
REVISION		A				
OUTLINE		O				

UNCONTROLLED DOCUMENT

