



RIVETS (4X)
 WHITE HOT STAMP ONE SIDE (SEE CHART)
 BAR CODE OR DATE CODE (SEE NOTES)

% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:

- INTERRUPT RATING: 2000A @ 32VDC
- VOLTAGE RATING: 32VDC
- TEMP. RATING: -40°C - 125°C
- CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
- SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
- APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
- BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC	FINISH	
1	9	18	DRW	SCALE 03/15/02 FULL
2	10	19	PJM	DATE 03/15/02 SUPER DRW
3	12	20	CHK	DATE SUPER DRW
4	13	21	APPD	DATE FINISH GOOD WT GRAMS/PIECE
5	14	23		
6	15	33		
7	16	43		
8	17	53		
TOLERANCE UNLESS OTHERWISE SPECIFIED				
TWO PLACE DEC ±.25 [.01] FRACTION ±				
THREE PLACE DEC ±.100 [.004] ANGULAR ±1°				
TITLE				
CABLEPRO				
LTR		REVISION		CHK
A		60801 - RELEASE 03/15/02 PJM		
B		83705B- ADDED BAR CODE 5/21/04		JMB
C		84765B-ADD NOTES FOR BAR CODE 05/31/06		DHM

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

NOTES CRITICAL CHARACTERISTICS.

NOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

NOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT MUST BE WITHIN THE DIMENSIONAL LIMITATIONS AND LOCATED AS SHOWN IN THE DRAWING AND INITIALLY LOCATED TO THE DRAWING FOR MAXIMUM TOOL LIFE.

REVISION

DRWG. NO. 0496200.7XE

OUTLINE

DES PLAINES, ILLINOIS 60016

UNCONTROLLED DOCUMENT