



RIVETS (4X)

WHITE HOT STAMP ONE SIDE (SEE CHART)

BAR CODE OR DATE CODE (SEE NOTES)

% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S

NOTES:
 INTERRUPT RATING: 2000A @ 32VDC
 VOLTAGE RATING: 32VDC
 TEMP. RATING: -40°C - 125°C
 CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
 SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
 APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
 BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

COMPONENT NO		DESCRIPTION		QTY/M	U/M
BILL OF MATERIAL					
MATERIAL SPEC		FINISH			
COPIES TO	DRW	DATE	SCALE	FULL	
1	9 18	12/03/03			
2	10 19		SUPER DRW		
3	12 20				
4	13 21		FINISH GOOD WT	GRAMS/PIECE	
5	14 23				
6	15 33				
7	16 43		TOLERANCE UNLESS OTHERWISE SPECIFIED		
8	17 53		TWO PLACE DEC ±.25[.01] FRACTION ±		
			THREE PLACE DEC ±.100[.004] ANGULAR ±1°		
3RD ANGLE PROJECTION		TITLE			
		CABLEPRO			
		DRAWG. NO.		OUTLINE	
		C		0496200.7XP	

LTR	REVISION	CHK	APD
A	61316 - RELEASED 12/03/03 PJM		
B	83705B- ADDED BAR CODE 5/21/04	JMB	
C	84765B-ADD NOTES FOR BAR CODE 05/31/06	DHM	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES.
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND PACKAGING TO BE DEFINED IN INSTRUCTIONS.
 DIMENSIONS CP DIMENSIONS.-MINIMUM CP VALUE
 DIMENSIONS TO BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO THE DIMENSION FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT

