



NOTES:

- INTERRUPT RATING: 2000A @ 32VDC
VOLTAGE RATING: 32VDC
TEMP. RATING: -40°C - 125°C
CABLE TYPE: XLPE, SAE J1127, STX (4AWG)
SPECIFICATION: MEETS LITTELFUSE'S VS-006013 SPECIFICATION
APPLICATION: DESIGNED FOR UNDERHOOD INSTALLMENT.
BAR CODE OR DATE CODE: THE BAR CODE OR DATE CODE IS USED FOR LOT TRACEABILITY. IT IS LOCATED ON ONE OF THE CABLE LEADS.

% OF RATING	OPENING TIME	
	MINIMUM	MAXIMUM
100	100 HRS.	-
135	120 S	1800 S
200	10 S	300 S
350	1 S	15 S
600	0.3 S	5 S



NO		COMPONENT NO	DESCRIPTION		QTY/M	U/M
BILL OF MATERIAL						
MTRL SPEC			FINISH			
COPIES TO		DRW	PJM	DATE	SCALE	FULL
1	9	18			12/03/03	
2	10	19	CHK			SUPER DRW
3	12	20				
4	13	21				
5	14	23	APPD			FINISH GOOD WT
6	15	33				GRAMS/PIECE
7	16	43	TOLERANCE UNLESS OTHERWISE SPECIFIED			
8	17	53	TWO PLACE DEC ±.25[.01] FRACTION ±			
3RD ANGLE PROJECTION		THREE PLACE DEC ±.100[.004] ANGULAR ±1°				
TITLE		CABLEPRO				
REVISION		DRAWG. NO.		OUTLINE		
C		0496200.7XL				
LITTELFUSE®						
DES PLAINES, ILLINOIS 60016						

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
DENOTES CRITICAL CHARACTERISTICS.
DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE
DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND PACKAGING MUST BE DEFINED IN INSTRUCTIONS.
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
DENOTES CRITICAL CHARACTERISTICS.
DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE
DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND PACKAGING MUST BE DEFINED IN INSTRUCTIONS.

UNCONTROLLED DOCUMENT