


CONTACT ARRANGEMENT



PRESCRIPTIONS

Nominal working voltage: 24V continuous voltage
Voltage range: 19.2 ÷ 32 V
Maximum contact current: 5A
Nominal contact current: 2A
Maximum power supply circuit current(30) in ON: 40mA
Maximum power supply circuit current(30) in OFF: 10 mA
Maximum control circuit current (86): 10 mA
Number of electrical operations: 200.000
Number of mechanical operations: 200.000
Delay on de-energization: 6(±1) sec.

SAP drawing number: 10000115059

Material and treatments:



Expertise Applied | Answers Delivered

TITLE
RELAY TIME DELAY DE-ENERGIZ. 6 SEC.

SIZE: A3	DWG. NO. OL-05930600	OUTLINE REV. A
-----------------	-----------------------------	-----------------------

SCALE 2:1 SHEET 1 OF 1