



REVISIONS				
REV.	DESCRIPTION	DATE	DESIGNED	APPROVED
A	First issue of outline drawing	02-Feb-21	L.Dal Molin	M.Tinto



SCALE 1:2

11	Nut M10	Brass	2	EA
10	Spring washer	Bronze	2	EA
9	Plane washer 10.2x18x2	Brass	2	EA
8	Power stud M10 short	Copper	2	EA
7	Fixing nut for screw	Copper	2	EA
6	Body connector	PBT	1	EA
5	OR ring	Silicon	1	EA
4	Self-tapping screw TCCIC 3x12	Steel	4	EA
3	Top cover	Thermosetting	1	EA
2	Screw M4x20	Steel	4	EA
1	Box short connector screws	PBT	1	EA
POS.	DESCRIPTION	MATERIAL	Q.TY	U/M

DOCUMENTO CORRELATO AL CERTIFICATO:
DOCUMENT CORRELATED TO THE CERTIFICATE:

AR 17 ATEX 022X

Non sono ammesse modifiche
senza l' approvazione
della "Persona Autorizzata".
No modify is allowed without the
"Authorized Person" approval.

PRESCRIPTIONS:


- Torque of screw M10=19 Nm max
- Fix the device with M6 screw and with torque of 6±2 Nm
- (&) Provided in the kit
- (\$) p/N of product

CHARACTERISTICS:

- Nominal voltage: 12V or 24V
- Working current main contact: 250A
- Max current main contact: 2000A for 5 sec.

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101:2017.							
linear dimensions							
0,5	>3	>6	>30	>120	>400	>1000	
3	6	30	120	400	1000	2000	
±0,1	±0,1	±0,2	±0,3	±0,5	±0,8	±1,2	
angle (for range of lengths)							
up to 10	>10	>50	>120	>400	>1000	>2000	
±1°		±0°'30'	±0°'20'	±0°'10'			
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL						
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL						
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE						
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS						
CP	DENOTES CP DIMENSIONS - MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE						
NAME		DATE		 Littelfuse® Expertise Applied Answers Delivered			
DRAWN	L. Dal Molin		02-Feb-21				
CHECKED	-	-					
	-	-					
FORM NO. CVP-PE40-0013 REV A				TITLE			
FIRST ANGLE PROJECTION				TGC/MGDE-I 12-24V DIN 7P			
		SIZE: A2		DWG. NO. OL-08075200		REV. A	
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 1 OF 1			