


PART No.	WIRE GA. / COLOR	"A" (REF)	"B"	"C"
OFNY0002ZXJ	# 12 ORANGE	266.7 (10.5)	9.65±2 (.38)	9.65±2 (.38)



- NOTES:
- 1. DIMENSION "A" MEASURED WITH FUSE INSTALLED.
 - 2. MAX RATING: 30A, 32VDC.
 - 3. MAX. TEMPERATURE: 80°C.
 - 4. WIRE: COPPER STRANDED, GXL.
 - 5. CONTACTS: C1100 ALLOY.
 - 6. CRIMP: MUST MEET USCAR 21 STANDARD.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CPK DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE

CPK DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. (PROCEDURE FOR MEASUREMENT OF CPK IS LOCATED IN THE FUSE INSPECTION INSTRUCTIONS.

CPK DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

CPK DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. (PROCEDURE FOR MEASUREMENT OF CPK IS LOCATED IN THE FUSE INSPECTION INSTRUCTIONS.

COPIES TO		MATERIAL SPEC		FINISH		TITLE	
1	9 18	DRW	DHM	DATE	09/05/08	SCALE	1=1
2	10 19	CHK		DATE		SUPER DRW	
3	12 20			DATE		RAW STK WT	LBS/M
4	13 21	APPD		DATE			
5	14 23						
6	15 33						
7	16 43						
8	17 53						
						TOLERANCE UNLESS OTHERWISE SPECIFIED	
						TWO PLACE DEC ±.01	
						THREE PLACE DEC ±.005	
						ANGULAR ±1°	
						FUSEHOLDER, INLINE (WITH FUSE)	
						OUTLINE	
						OFNY0002ZXJ	

LTR	REVISION	CHK	APD
A	000490ER-RELEASED 9/05/08	DHM	

Littlefuse
DES PLAINES, ILLINOIS 60016