


COLE-HERSEE CO.

|        |       |
|--------|-------|
| IN     |       |
| .25    | .010  |
| 4.74   | .187  |
| 28.44  | 1.120 |
| 38.10  | 1.500 |
| 47.49  | 1.870 |
| 107.95 | 4.250 |

1160



DO NOT SCALE

| LET | WAS | DATE | BY | LET | WAS        | DATE   | BY | MATERIAL     | DRAWN                                              | CHECKED | APPRV D | SCALE | DATE DRAWN     |
|-----|-----|------|----|-----|------------|--------|----|--------------|----------------------------------------------------|---------|---------|-------|----------------|
|     |     |      |    |     |            |        |    | — # —        | P. 3.                                              | 4-22-77 |         | 1:1   | 7-9-47         |
|     |     |      |    |     |            |        |    | FINISH       | COLE-HERSEE COMPANY<br>BOSTON, MASS. 02127, U.S.A. |         |         |       | DATE BLUEPRINT |
|     |     |      |    |     |            |        |    | — # —        |                                                    |         |         |       |                |
|     |     |      |    | V   | REV/200 14 | 2-3-78 | JV | TOLERANCES   | LICENSE CARRIER                                    |         |         |       | 1160           |
|     |     |      |    |     | REV/200 14 | 2-3-78 | JV | FRACTIONAL ± |                                                    |         |         |       |                |
|     |     |      |    |     |            |        |    | DECIMAL ±.25 |                                                    |         |         |       |                |

SPAULDING CO., INC 21-5353