

24512-16	12	18.6	CONTINUOUS	14	7.5	COPPER	F	ASSEMBLED				RATING: 80 AMPS
P-24512-15	12	18.6	CONTINUOUS	14	7.5	COPPER	F	BULK				RATING: 80 AMPS
24512-15	12	18.6	CONTINUOUS	14	7.5	COPPER	F	BAGGED				RATING: 80 AMPS
24512-14	12	3.8	INTERMITTENT	14	8.5	COPPER	F	ASSEMBLED				
P-24512-13	12	3.8	INTERMITTENT	14	8.5	COPPER	F	BULK				
24512-13	12	3.8	INTERMITTENT	14	8.5	COPPER	F	BAGGED				
P-24512-12	12	3.8	INTERMITTENT	14	8.5	SILVER	F	BULK				
24512-12	12	3.8	INTERMITTENT	14	8.5	SILVER	F	BAGGED				
24512-11	12	18.6	CONTINUOUS	14	7.5	SILVER	F	ASSEMBLED				
P-24512-10	12	18.6	CONTINUOUS	14	7.5	SILVER	F	BULK				
24512-10	12	18.6	CONTINUOUS	14	7.5	SILVER	F	BAGGED				
24512-06	12	18.6	CONTINUOUS	14	7.5	COPPER	L	ASSEMBLED				RATING: 80 AMPS
P-24512-05	12	18.6	CONTINUOUS	14	7.5	COPPER	L	BULK				RATING: 80 AMPS
24512-05	12	18.6	CONTINUOUS	14	7.5	COPPER	L	BAGGED				RATING: 80 AMPS
24512-04	12	3.8	INTERMITTENT	14	8.5	COPPER	L	ASSEMBLED				
P-24512-03	12	3.8	INTERMITTENT	14	8.5	COPPER	L	BULK				
24512-03	12	3.8	INTERMITTENT	14	8.5	COPPER	L	BAGGED				
P-24512-02	12	3.8	INTERMITTENT	14	8.5	SILVER	L	BULK				
24512-02	12	3.8	INTERMITTENT	14	8.5	SILVER	L	BAGGED				
24512-01	12	18.6	CONTINUOUS	14	7.5	SILVER	L	ASSEMBLED				
P-24512	12	18.6	CONTINUOUS	14	7.5	SILVER	L	BULK				
24512	12	18.6	CONTINUOUS	14	7.5	SILVER	L	BAGGED				
PART NO	V DC	OHMS	DUTY	MAX VOLT.	PULL-IN VOLT.	CONTACT MATERIAL	BRACKET STYLE	HARDWARE NOTE 7				ADDITIONAL NOTES
	COIL RATINGS											