

Push Button Switches

Heavy-Duty Normally Open



90030-04



9100



9245



9095



9231

Description

Littelfuse Heavy-duty Normally Open Push Button Switches are push to operate and will spring return to 'Off' position. They have a cylindrical diecast body with 5/8"-32 mounting stem.

These normally open switches are impact resistant, designed to prevent accidental actuation, include two screw terminals, and have an O-Ring seal in the mounting stem.

Specifications

Housing:

Base: Cylindrical Diecast Body

Face nut and Button: Chrome Plated

Circuitry:

Normally Off (Circuit only closing with actuator depressed, with spring return to 'Off')

Rating:

35A @ 12V DC
20A @ 24V DC

Contacts:

Silver

Web Resources

Download installation instructions, 2D prints and technical resources at: littelfuse.com/HDPushButtonSwitches

Push Button Switches

Heavy-Duty Normally Open

Ordering Information

PART NUMBER BULK	PART NUMBER BOX	PART NUMBER RETAIL	DESCRIPTION	MOUNTING	TERMINALS
9100	—	9100-BP	Momentary Push Button Switch	15/32"-32 21/32"L (16.7mm)	2 Screws
9023	902-BX	9023-BP	15A resistive, 10A inductive at 12V DC, 8A resistive, 5A inductive at 24V DC	5/8"-32 7/8" L (22.1mm)	2 Screws
9023-09	—	—	15A resistive, 10A inductive at 12V DC, 8A resistive, 5A inductive at 24V DC. Screw-on black rubber cap 83280-03	5/8"-32 7/8" L (22.1mm)	2 Screws
9095	9095-BX	9095-BP	Compact Momentary Push Button Switch, 20A at 24V and 35A at 12V DC	5/8"-32 21/32"L (16.7mm)	2 Screws
9095-16	—	—	Compact Momentary Push Button Switch, 20A at 24V and 35A at 12V DC	5/8"-32 21/32"L (16.7mm)	2 Screws
9155	—	—	Momentary Starter Switch with Large Aluminum Button	5/8"-32 21/32"L (16.7mm)	2 Screws
9216	9216-BX	9216-BP	Industrial Starter Switch	5/8"-32 21/32"L (16.7mm)	2 Screws
9216-03	9216-03-BX	9216-03-BP	Same as 9216, but with Large Screw-on Black Rubber Cap 83280-03	5/8"-32 21/32"L (16.7mm)	2 Screws
9231	9231-BX	9231-BP	Heavy Duty Starter Switch with recessed facenut to protect actuator	5/8"-32 21/32"L (16.7mm)	2 Screws
9238	9238-BX	9238-BP	15A resistive, 10A inductive at 12V DC, 8A resistive, 5A inductive at 24V DC	5/8"-32 7/8" L (22.1mm)	2 Screws
9238-01	—	—	15A resistive, 10A inductive at 12V DC, 8A resistive, 5A inductive at 24V DC, Black rubber screw-on cap 83280-03	5/8"-32 7/8" L (22.1mm)	2 Screws
9245	9245-BX	—	O-ring seal in the mounting stem, and snap-on black rubber cap (407-03)	5/8"-32 21/32"L (16.7mm)	2 Screws
90000-01	—	—	With recessed facenut to protect button. O-ring seal	5/8"-32 21/32"L (16.7mm)	2 Screws
90011	—	—	Heavy Duty Momentary Switch with Black Plastic Button. Designed for 20A at 24V DC and 35A at 12V DC	5/8"-32 5/8"L (15.9mm)	2 Male Buttons Aptiv #2962679
90030	90030-BX	90030-BP	Heavy Duty Momentary Switch with screw-on Black Plastic Cap 83280-03. Designed for 20A at 24V DC and 35A at 12V DC	5/8"-32 21/32"L (16.7mm)	2 Screws
90030-04	—	90030-04-BP	Same as 90030, but with Red Screw-On Cap 83280-02	5/8"-32 21/32"L (16.7mm)	2 Screws
90030-53	—	—	Same as 90030, but shipped assembled	5/8"-32 21/32"L (16.7mm)	2 Screws
90036-02	90036-02-BX	90036-02-BP	Heavy Duty Compact Momentary Switch with Chrome-Plated Brass Actuator. Designed for 20A at 24V DC and 35A at 12V DC	5/8"-32 21/32"L (16.7mm)	2 Blades
90036-10	—	—	Compact Momentary Push Button Switch, 20A at 24V and 35A at 12V DC with Red Cap (White Horn Logo Imprint)	5/8"-32 21/32"L (16.7mm)	2 Blades
90043-07	90043-07-BX	90043-07-BP	PVC-Coated Momentary Push Button Switch, 15A at 12V DC, with Black Cap	5/8"-32 21/32"L (16.7mm)	2 Wire Lead
92120	—	—	Momentary Push Button Indicator Switch, 3A at 24V and 5A at 12V DC	3/8"-24 21/32"L (16.7mm)	2 Screws
96101	96101-BX	96101-BP	Push Button Horn Switch, with Black Cap	Surface Mount, 44.45mm between 2 Screws	2 Screws