






THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	GCF #524724 INITIAL RELEASE. DSILVA.	1/25/2022	L.ARGIL



- NOTES:
- GENERAL TOLERANCES: DIN 16901-130
 - BASE RESIN: POLYETHYLENE (PET)
 - FLAME RETARDANT
 - COLOR: BLACK (ACCORDING BASE RESING)

NO.		COMPONENT NO.		COMPONENT NAME						QTY		U	
TOLERANCES ULESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)													
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400									ANGLE
±0.05	±0.05	±0.1	±0.15	±0.2									NONE
DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.													
PER CHI-NPDP20-0008 PROCEDURE			FIT/ FUNCTION CRITICAL CHARACTERISTICS										
	<S>		SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL										
	CPK		DENOTES CPK DIMENSIONS MINIMUM CPK VALUE										
			DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS										
	CP		DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE										
		NAME		DATE		Littelfuse® Expertise Applied Answers Delivered TITLE FKH HALTER SCHWARZ							
DRAWN		D.SILVA		1/5/2022									
CHECKED		-		-									
		-		-									
		-		-									
FORM NO: CVP-PE40-0003 REV B						SIZE B DWG. NO. OUTLINE OL-371.6150.0000 REV. A							
THIRD ANGLE PROJECTION													
													
DO NOT SCALE DRAWING													
SCALE 2:1													
SHEET 1 OF 1													