






REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	ECN# 00024	TY	1/14/2020
	B	ECO #523271 - ADD SPECIFICATION NOTE RELATED TO ADD STICK LABEL & WHITE BOX PACKAGING	2/10/2021	S CASTILLO



- NOTES:
1. ALL STEEL PARTS ARE PLATED.
 2. ALL DIMENSIONS ARE REFERENCE ONLY.
 3. PACK SOLENOID IN WHITE BOX CA-531 AND STICK LABEL 663 (PROP. 65) IN BOX.

MM
[INCH]

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.						
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF.ISO2768-M) FOR METAL, REF.SPI PLASTICS						
DIMENSION MM	UP TO 0.5 - 3	OVER 3 - 6	OVER 6 - 30	UP TO 30 - 120	OVER 120 - 400	ANGLE
TOLERANCES	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5°
DRAWN	NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered			
CHECKED	TY	09/14/99				
	-	-				
	-	-				
FORM NO: CVP-PE40-0005 REV A			TITLE			
THIRD ANGLE PROJECTION			SOLID STATE SOLENOID			
		SIZE C	DWG. NO. 48785	REV. B		
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 1 OF 1		