


55020-04

MM	IN
25	.010
96	.038
1.82	.072
9.82	.373
11.93	.470
15.74	.620
26.16	1.030
28.44	1.120
203.20	8.000



NOTE
1 NEOPRENE O RING SEALED

(A)

METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRO'D	SCALE	DATE DRAWN
									PM	8379			7-27-79
								FINISH					DATE BLUEPRINT
				A	DELETED NOTE	3-29-84	PR	TOLERANCES					
					ADDED NOTE			DECIMAL ± .00					
					ISSUED	8-3-79	Y	METRIC ± .00					
S.P.S.T. MOM TOGGLE SWITCH										55020-04			

CH 188(4 78)