

MM	IN
25	.010
228	.090
8.63	.340
17.01	.670
17.27	.680
21.08	.830
22.86	.900
27.94	1.100
30.22	1.190
31.49	1.240
36.83	1.450
39.87	1.570





56006-01
56006-05

ROCKER, WHITE

BEZEL, NICKEL PLT. BRIGHT FINISH.

INSULATOR

SCREW TERMINAL
6-32 UNC (6 PLACES)

METRIC

NOTES:

1. SILVER CONTACT SURFACES.
2. HEAVY DUTY.
3. 25 AMPS @ 12 VDC LAMP LOAD.
4. ALL STEEL PARTS PLATED.
5. ALL DIM'S ARE REF. ONLY.

56006-05 SAME AS 56006-01
EXCEPT BEZEL NICKEL PLT.
DULL FINISH

LET.	WAS	DATE	BY LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROVD.	SCALE	SUBSTITUTE W/K/A/R/V/W	DO NOT SCALE
							//	CF			1 : 1	560006 W/K/A/R/V/W BEZEL REPLACING BRACKET	9-22-67 DATE DRAWN
							FINISH //						DATE BLUEPRINT
							TOLERANCES DECIMAL ± METRIC ±						
			(G)	REDRAWN NO CHANGE	1-5-83	(R)						D.P.-D.T. ROCKER SWITCH	560006-01 560006-05

CH-188(4-78)