



MM	IN
.25	.010
12.70	.500
13.71	.540
17.27	.680
21.08	.830
24.38	.960
30.22	1.190
36.83	1.450
40.68	1.601
43.18	1.700


57014-03



MTG. HOLE DETAIL



METRIC



- NOTES: (C)
- 1. WEATHERPROOF
 - 2. SILVER CONTACTS
 - 3. HEAVY DUTY
 - 4. 25 AMPS @ 12 VDC LAMP LOAD
- DO NOT SCALE**

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV'D	SCALE	BASIC DIMENSIONS	DATE DRAWN
				C	REV. 21346	5-20-81	(B)	H	(R)	RA		1:1	WEATHERPROOF	10-2-80
				B2	WAS MDM ON 1, 4 / 21239	11-24-80	(C)	FINISH						DATE BLUEPRINT
				B1	WAS MDM ON 2, 5 / 21239			H						
E	ECN 24267	1-31-90	RA		ISSUED	10-9-80	RA	TOLERANCES						
D	ECN 23335	12-11-80	WA	A	WHINE	10-9-80	RA	DECIMAL ±, METRIC ±.25					REVERSING ROCKER SWITCH	57014-03

CH-188(4-78)