

T 3,15 A L 250V**Speed:**

T = Time Delay

F = Fast

M = Medium

TT = Very slow

FF = Very fast

Current Rating:

1A, 5A, 32mA (.032A)

Breaking Capacity:

L = Low (glass)

H = High (ceramic)

E = Enhanced (glass)

Voltage Rating:Maximum circuit voltage at
rated interrupting current