

8/66


PART NO.	KNOB NO. (COLOR)	WORDING	COLOR	STYLE
8166-	8150-			
-13	8150-B1 (BLACK)	SWITCH	WHITE	I
-12	81367 (DULL BLACK)	NONE	—	—
-11	8150-B4 (YELLOW)	NONE	—	—
-10	B1 (TAN)	NONE	—	—
-09	B1 (BLACK)	WIPER	WHITE	I
-08	B1 (BLACK)	PANEL LIGHTS	WHITE	II
-07	B1 (BLACK)	PANEL LAMPS	WHITE	II
-06	B1 (BLACK)	LIGHTS	WHITE	I
-05	B1 (BLACK)	HEATER	WHITE	I
-04	B1 (BLACK)	FAN	WHITE	I
-03	B1 (BLACK)	DOME LIGHT	WHITE	II
-02	B2 (IVOARY)	NONE	—	—
8166-01	8150-B1 (BLACK)	NONE	—	—
		IMPRINTING		

8166-KNOB
SEE CHART





STYLE I

8-32 TAPPED HOLE
1/32 X 45° CHAMFER



80264 INSERT
ALUM.-8200
SET SCR STEEL
8-32

-IMPRINTING
(SEE CHART)



-Ø SET SCREW

STYLE II (STYLE I EXCEPT IMPRINTING)

STYLE III (STYLE II EXCEPT IMPRINTING)

SEE SEPARATE DRAWING
FOR IMPRINTING

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D.	SCALE	DATE DRAWN
				N	ADD 18094	4-6-73	RT	NOTED	MW.	REB		2X	9-1-50
				M	COLOR ADDED TO KNOB COL.	3-15-73	R.B.	FINISH NOTED	COLE-HERSEE COMPANY BOSTON, MASS. 02127, U.S.A.				DATE BLUEPRINT
				L	COLOR ADDED TO KNOB COL.	2-27-73	R.B.						
				K	9166-26 17975	1-12-73	C.B.	TOLERANCES FRACTIONAL $\pm$ DECIMAL $\pm$.01	KNOB S.A.				8166
P	18501-110D 1856-08	3/24/73	142	J	REV. 17866	9-18-72	B						

SPAIN (DINO) 22