


SOURCE:
DYNAMIC INDUSTRIES
DY-23808

MM	IN
88	.035
99	.039
279	.110
317	.125
553	.218
784	.309
939	.370
965	.380
1143	.450
2514	.990
2565	1.010
3860	1.520



NOTE:
1. SWITCH TO OPERATE AT
60 TO 120 PSI PRESSURE

METRIC

DO NOT SCALE

LET.	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL —H—	DRAWN AA	CHECKED 	APPR'D	SCALE 1=1	DATE DRAWN 4-17-56
								FINISH —H—	 Cole Hersee Co. 20 OLD COLONY AVENUE SOUTH BOSTON MA U.S.A. 02127				DATE BLUEPRINT
								TOLERANCES	SWITCH STOPLAMP				8638
				D	RELDRAWN	6-21-89	JK	DECIMAL ± METRIC ±					

CH-188(4-78)

Confidential Property of Cole Hersee