


1. STANDING FLASH 0.025 MAXIMUM PERMISSIBLE AT PARTING LINE.
2. STANDING FLASH 0.010 MAXIMUM PERMISSIBLE ALL OTHER AREAS.
3. MATERIAL SPECIFICATION:
HIGH CONSISTENCY RUBBER (HCRP)
4. CAVITY NUMBER AND MOLDING GATES PERMITTED ON THIS SURFACE. MAXIMUM HEIGHT 0.007.



868-096	GRAY	.173 DIA
868-095	BLUE	.115 DIA
PART NO	COLOR	DIA ^o "A"

NO		COMPONENT NO		DESCRIPTION		QTY/M	U/M		
BILL OF MATERIAL									
		COPIES TO		MATL SPEC	SEE NOTE 3	FINISH			
1		9	18	DRW	DHM	DATE	05/23/08		
2		10	19			SCALE	2 : 1		
3		12	20	CHK		DATE	SUPER DRW		
4		13	21			DATE			
5		14	23	APPD		DATE	RAW SIK WT		
6		15	33				LBS/M		
7		16	43			TOLERANCE UNLESS OTHERWISE SPECIFIED			
8		17	53			TWO PLACE DEC ± .01			
						THREE PLACE DEC ± .005			
						ANGULAR ± 1°			
TITLE									
SEAL SPLASH-PROOF MAXI FUSE HOLDER									
				REMOVAL A		DRAWG. NO. 868-095 868-096			
DES PLAINES, ILLINOIS 60016									
LTR		REVISION						CHK	APD
A		000402ER - RELEASED 05/23/08 DHM							