



APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259

95522

(2) .125 DIA DRAIN HOLES
DIAMETRICALLY OPPOSITE
KEY-STEEL- (SEE CHART)


OFF
40°
ON
BAT. IGN.



A" TYPE SWITCH SHOWN

Confidential Property of Cole Hersee

95522 B	83353-2 KEYS RINGED
95522 A	83357-2 KEYS RINGED
95522 BASIC	_____
SWITCH NO.	KEY PART NO.



OPTIONAL KEY

NOTE:
1. O" RING SEALED AT
BUSHING
2 ALL STEEL PARTS PLATED
10 AMPS @ 12 VDC

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPR'D.	SCALE		DO NOT SCALE
				L	NOTE 2 ADDED	2/25/34	11/17/92	TH		EA			FULL	DATE DRAWN 12-12-62
				K	CAD	18606	6-12-74	DD		COLE-HERSEE COMPANY				DATE BLUEPRINT
				J	SAE SPEC ADDED		3/14/74	JW		BOSTON, MASS. 02127, U.S.A.				
				I	REV	18038	3-5-73	RB	TOLERANCES FRACTIONAL ± DECIMAL ± .01	WEATHERPROOF IGNITION SWITCH				95522
				H	REDRAWN NO CHANGE		2-16-72	CT						
10	Removed Part 2	7/15/01												