


| MM    | IN.   |
|-------|-------|
| 125   | .010  |
| 3.17  | .125  |
| 6.35  | .250  |
| 22.09 | .870  |
| 47.24 | 1.860 |
| 67.31 | 2.650 |


COLE-HERSEE CO.

95532

APPLICABLE SAE  
STANDARD OR RECOMMENDED  
PRACTICE SAE J259



Confidential Property of Cole Hersee



NOTE:  
① ALL STEEL PARTS PLATED

METRIC

| LET                         | WAS | DATE | BY | LET | WAS                | DATE     | BY   | MATERIAL     | DRAWN | CHECKED                 | APPR'D. | SCALE | DO NOT SCALE   |
|-----------------------------|-----|------|----|-----|--------------------|----------|------|--------------|-------|-------------------------|---------|-------|----------------|
|                             |     |      |    | M   | ECN 06023          | 2/2/66   | S/G  | —#—          | PH    | TY                      |         | 1:1   | DATE DRAWN     |
|                             |     |      |    | L   | CAD OR ZINC 125234 | 11/17/92 | T.H. | FINISH       |       |                         |         |       | 12-11-61       |
|                             |     |      |    | K   | ECN 2339A          | 2-2-87   | L.B. | —#—          |       |                         |         |       | DATE BLUEPRINT |
|                             |     |      |    | W   | EXA/19872          | 3-8-77   | K    | TOLERANCES   |       |                         |         |       |                |
|                             |     |      |    | H   | REV. 19872         | 5-6-77   | K    | FRACTIONAL ± |       |                         |         |       |                |
|                             |     |      |    |     |                    |          |      | DECIMAL ±.25 |       |                         |         |       |                |
| COLE-HERSEE COMPANY         |     |      |    |     |                    |          |      |              |       | 2 POSITION IGNITION SW. |         |       | 95532          |
| BOSTON, MASS. 02127, U.S.A. |     |      |    |     |                    |          |      |              |       |                         |         |       |                |